



Sample photo

**Order symbol:** ALN 061005  
**Product nbr:** 7811080  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074016041  
**EI. number:**  
 Finland: 3420042  
 Electric No. 8212045622  
 Denmark:  
 Electric No. Sweden: 2536307

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	100	66	46	MR 75003 Selftapping taptite screw M3
inch:	3.9	2.6	1.8	MRS 28540 Wall fastening lug (2 pcs)

Materials:	Rating:
<b>Material:</b> Aluminium	Ingress Protection (EN 60529): IP66/IP67/IP68
<b>Base colour:</b> RAL 7001	Impact Resistance (EN 62262): IK08
<b>Cover screws material:</b> Stainless steel	NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Cover colour:</b> RAL 7001	<b>Certificates:</b>
<b>Gasket material:</b> Polyurethane	SGS Fimko

Temperatures:
<b>Temperature °C (short term):</b> -50 ... 140 °C
<b>Temperature °C (continuous):</b> -50 ... 80 °C
<b>Temperature °F (short term):</b> -60 ... 285 °F
<b>Temperature °F (continuous):</b> -60 ... 175 °F

Accessories:
ARM 0610 DIN-15 Mounting rail

