



Sample photo

Order symbol: ALN 081306
Product nbr: 7811150
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016072
EI. number:
 Finland: 3420045
 Electric No. 8212045651
 Denmark:
 Electric No. Sweden: 2536313

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	127	81	57	ARM 0813	DIN-15 Mounting rail
inch:	5.0	3.2	2.2	MR 75003	Selftapping taptite screw M3
				MRS 28540	Wall fastening lug (2 pcs)

Materials:		Rating:
Material:	Aluminium	Ingress Protection (EN 60529): IP66/IP67/IP68
Base colour:	RAL 7001	Impact Resistance (EN 62262): IK08
Cover screws material:	Stainless steel	NEMA Class: NEMA 1, 4, 4X, 12, 13
Cover colour:	RAL 7001	
Gasket material:	Polyurethane	

Temperatures:	
Temperature °C (short term):	-50 ... 140 °C
Temperature °C (continuous):	-50 ... 80 °C
Temperature °F (short term):	-60 ... 285 °F
Temperature °F (continuous):	-60 ... 175 °F

Accessories:	
AM 0813	Mounting plate

