



Sample photo

Order symbol: ALN 161609
Product nbr: 7811270
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016126
EI. number:
 Finland: 3420051
 Electric No. Denmark: 8212045716
 Electric No. Sweden: 2536325

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	163	162	91	ARM 0615	DIN-15 Mounting rail
inch:	6.4	6.4	3.6	ARH 16	DIN-35 Mounting rail
Materials:				MR 75005	Selftapping taptite screw M5
Material:	Aluminium			MRS 28541	Wall fastening lug (2 pcs)
Base colour:	RAL 7001			PH A & AH A/B	Hinge set
Cover screws material:	Stainless steel			Rating:	
Cover colour:	RAL 7001			Ingress Protection (EN 60529): IP66/IP67/IP68	
Gasket material:	Polyurethane			Impact Resistance (EN 62262): IK08	
Temperatures:				NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperature °C (short term):	-50 ... 140 °C			Certificates:	
Temperature °C (continuous):	-50 ... 80 °C			SGS Fimko	
Temperature °F (short term):	-60 ... 285 °F				
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:					
AM 1616	Mounting plate				

