



Sample photo

Order symbol: PCTQ3 122410
Product nbr: 7025780
Description: Enclosure, PC
Remarks: Smoked transparent cover (quick-locking)

EAN: 6418074099082
EI. number:
Finland: 3424190

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:			Accessories:		
Length	Width	Height			
mm:	244	124	97	TRM 0812	DIN-15 Mounting rail
inch:	9.6	4.9	3.8	MIN 20	DIN-15 Mounting rail
Materials:			TRH 1212	DIN-35 Mounting rail	
Material:	Polycarbonate		TRH 24	DIN-35 Mounting rail	
Base colour:	RAL 7035 -light grey		TF 28037	Wall fastening lug (4 pcs)	
Cover screws material:	Stainless steel		TH A	Grey plastic hinges (2 pcs)	
Cover colour:	Clear transparent		EU 3 QuickLock set 60	QuickLock screws (60 pcs)	
Gasket material:	Polyurethane		MR 28036EU Set 60	Mounting screws (60 pcs)	
			EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30	
			EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black	
Temperatures:			Rating:		
Temperature °C (short term):	-40 ... 120 °C		Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (continuous):	-40 ... 80 °C		Impact Resistance (EN 62262): IK07		
Temperature °F (short term):	-40 ... 250 °F		Electrical insulation: Totally insulated		
Temperature °F (continuous):	-40 ... 175 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
			Glow Wire Test (IEC 695-2-1) °C: 650		
Accessories:			Certificates:		
TM 1224	Mounting plate		SGS Fimko		
			Gost R		

