



Sample photo

**Order symbol:** PCQ3 162409  
**Product nbr:** 7035811  
**Description:** Enclosure, PC  
**Remarks:** Grey cover (quick-locking)

**EAN:** 6418074099259  
**EI. number:**  
**Finland:** 3424239

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		244	164	95	MIN 20	DIN-15 Mounting rail	
inch:		9.6	6.5	3.7	TRH 24	DIN-35 Mounting rail	
<b>Materials:</b>						TF 28037	Wall fastening lug (4 pcs)
<b>Material:</b>	Polycarbonate					TH A	Grey plastic hinges (2 pcs)
<b>Base colour:</b>	RAL 7035 -light grey					EU 3 QuickLock set 60	QuickLock screws (60 pcs)
<b>Cover screws material:</b>	Stainless steel					MR 28036EU Set 60	Mounting screws (60 pcs)
<b>Cover colour:</b>	RAL 7035 -light grey					EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30
<b>Gasket material:</b>	Polyurethane					EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black
<b>Temperatures:</b>						<b>Rating:</b>	
<b>Temperature °C (short term):</b>	-40 ... 120 °C					Ingress Protection (EN 60529): IP66/IP67	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C					Impact Resistance (EN 62262): IK07	
<b>Temperature °F (short term):</b>	-40 ... 250 °F					Electrical insulation: Totally insulated	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F					Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Accessories:</b>						Glow Wire Test (IEC 695-2-1) °C: 650	
TM 1624	Mounting plate					<b>Certificates:</b>	
						SGS Fimko	
						Gost R	

