



Sample photo

Order symbol: PCQ3 163610
Product nbr: 7035751
Description: Enclosure, PC
Remarks: Grey cover (quick-locking)

EAN: 6418074099310
EI. number:
Finland: 3424259

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	360	160	96	ARM 0615	DIN-15 Mounting rail
inch:	14.2	6.3	3.8	DH-3	DIN-35 Mounting rail
Materials:				TRH 2036	DIN-35 Mounting rail
Material:	Polycarbonate			TF 28037	Wall fastening lug (4 pcs)
Base colour:	RAL 7035 -light grey			TH A	Grey plastic hinges (2 pcs)
Cover screws material:	Stainless steel			EU 3 QuickLock set 60	QuickLock screws (60 pcs)
Cover colour:	RAL 7035 -light grey			MR 28036EU Set 60	Mounting screws (60 pcs)
Gasket material:	Polyurethane			EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30
Temperatures:				EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black
Temperature °C (short term):	-40 ... 120 °C			Rating:	
Temperature °C (continuous):	-40 ... 80 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °F (short term):	-40 ... 250 °F			Impact Resistance (EN 62262): IK07	
Temperature °F (continuous):	-40 ... 175 °F			Electrical insulation: Totally insulated	
Accessories:				Halogen free (DIN/VDE 0472, Part 815): 1	
TM 1636	Mounting plate			Glow Wire Test (IEC 695-2-1) °C: 650	
				Certificates:	
				SGS Fimko	
				Gost R	

