



Sample photo

**Order symbol:** PCTQ3 163610  
**Product nbr:** 7025750  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover (quick-locking)

**EAN:** 6418074099327  
**EI. number:**  
**Finland:** 3424261

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		360	160	95	ARM 0615	DIN-15 Mounting rail	
inch:		14.2	6.3	3.7	DH-3	DIN-35 Mounting rail	
<b>Materials:</b>					TRH 2036	DIN-35 Mounting rail	
<b>Material:</b>		Polycarbonate		TF 28037	Wall fastening lug (4 pcs)		
<b>Base colour:</b>		RAL 7035 -light grey		TH A	Grey plastic hinges (2 pcs)		
<b>Cover screws material:</b>		Stainless steel		EU 3 QuickLock set 60	QuickLock screws (60 pcs)		
<b>Cover colour:</b>		Clear transparent		MR 28036EU Set 60	Mounting screws (60 pcs)		
<b>Gasket material:</b>		Polyurethane		EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30		
<b>Temperatures:</b>					EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black	
<b>Temperature °C (short term):</b>		-40 ... 120 °C		<b>Rating:</b>			
<b>Temperature °C (continuous):</b>		-40 ... 80 °C		Ingress Protection (EN 60529): IP66/IP67			
<b>Temperature °F (short term):</b>		-40 ... 250 °F		Impact Resistance (EN 62262): IK07			
<b>Temperature °F (continuous):</b>		-40 ... 175 °F		Electrical insulation: Totally insulated			
<b>Accessories:</b>					Halogen free (DIN/VDE 0472, Part 815): 1		
TM 1636		Mounting plate		Glow Wire Test (IEC 695-2-1) °C: 650			
<b>Certificates:</b>					SGS Fimko		
					Gost R		

