

Model	H39N2600UK
Front-cover Material/Color	Plastic/ black
Back-cover Material/Color	Plastic/ black
TV Type	FHD Feature TV
Panel Performance	
Panel Aspect Ratio	16:09
Screen Size (diagonal)	39inch
Screen Size (diagonal) CM	98
Max. Resolution	FHD 1920x1080
Curvature Rate	-
Angle of visibility	178°
Display Color Depth	8bits
TCON color depth	8bits
Color gamut range BT.2020	52% (BT.2020)
Vsync Frequency	60Hz
Contrast	5000:1(type)
TV Brightness (nits) (lowest)	200nit
TV Brightness (nits) (Typical Value)	220nit
TV Peak Brightness (nits) and Duration (s)	-
Backlight technology	DLED
Quantum Dot Technology	No
Local Dimming	No
Local Dimming Zones	No
FRC	No
3D technology	No
2D to 3D	No
PCI(Picture Criteria Index)	800
HDR technology	No
HDR Classification	No
Improving Engines	
Processor	Mstar MSD3463GLAT-SW
Upscaling Ultra HD	No
MEMC	No
Decoder	HEVC (H.265),H.264,MPEG4, MPEG2
Input Lag in Game Mode	<50 ms
3D Digital Comb Filter	Yes
MPEG noise reduction	Yes
Mosquito noise reduction	Yes
Sound	
Sound output power	2x7W
Sound Technology	-
NICAM / A2 Stereo	NICAM Stereo
User Equalizer	No
Sound - Special	Dolby Digital AC3
Convenience	
Media Player	Yes(Video,Audio,Picture)
Multi-Language OSD	15Languages
Hotel TV	Yes

User Interface	Yes
Internet	
Important Apps (all countries)	No
Country-specific apps	No
Web browser	No
HbbTV	No
MHEG support	No
Anyview Cast	No
Anyview Stream	No
Reception and TV Features	
Digital and Analog Tuner	DVB-T2/T/C/S2/S
Twintuner	No
LCN Support	Yes
Teletext Support	Yes
EPG	Yes
Parental Control	Yes
PVR	No
Time Shift	No
Channel sorting	No
Favorite channel list	Yes
Connectivity	
Common Interface (CI+)	Yes(V1.3)
HDMI1	HDMI 1.4,CEC,ARC
HDMI2	HDMI1.4,CEC
HDMI3	HDMI1.4,CEC
HDMI4	-
USB (2.0)	1
USB (3.0)	0
S/PDIF Output	1(optical)
Audio (L/R) Input	1
Headphone Output	1
RF Tuner	2
Composite (AV) Input	1
Component YPb(Cb)/Pr(Cr) Input	1
SCART	1 (Scart in only)
VGA Input	1
PC Audio Input (3.5mm)	1
Subwoofer	No
Ethernet RJ45 port	No
Wireless LAN adapter Support	No
WiFi technology	No
Bluetooth Support and profiles	No
Eco & Power supply	
Power Supply	100V-240V 50/60Hz
Energy Efficiency Class	A+
Standby Consumption	<0.5W
Power off	0W
Power Consumption (Nameplate)	70W

Annual consumption (Nameplate)	-
Power Consumption (Energy Rating Label)	47W
Annual consumption (Energy Rating Label)	68kWh
Luminance Ratio	>65%
Mercury content	0 mg
Lead content	Yes -This television contains lead only in certain parts or components , in accordance with existing exemption clauses under the RoHS Directive.
Weight & Dimensions	
Weight incl. Packaging	9.4kg
Product weight incl. Stand	6.5kg
Product weight excl. Stand	6.4kg
Weight of carton box	2.0kg
Weight of plastic foam in package material	0.53kg
Weight of plastic in package material	0.05kg
Weight of metal in package material	0.02kg
Package (Horizontal/Vertical)	Vertical
Packaging Dimension (LxDxH)	985X149X610mm
Product Dimension incl. Stand (LxDxH)	886X203X564mm
Product Dimension excl. Stand (LxDxH)	886X84X517mm
Maximum distance between two stand(L)底座间最大尺寸	677mm
Accessories	
Stand Material / Color	Plastic/ black
Stand (LxW)	203x17.5mm
VESA Wall Mount Compatible	200*200mm
Remote control (Number of Keys / Model number)遥控器型号	ER-22601B
Second Remote Control (Model number)	No
Remote Batteries	AAAx2
User Manual	Yes
Quick start page	Yes
Power cable	Yes
Adapter	No
Units of packaging material	carton纸箱1pc+pad 衬垫3pc+TV's package bag整机袋1pc+accessary bag附件袋1pc+power line package bag电源线包装袋1pc++base stand package bag底座包装袋2pc+remote control package bag遥控器包装袋1pc+screw package bag底座螺钉包装袋1pc
Units of packaging material (0.1g < unit <= 0.5g)	screw package bag底座螺钉包装袋1pc
Units of packaging material (unit > 0.5g)	carton纸箱1pc+pad 衬垫3pc+TV's package bag整机袋1pc+accessary bag附件袋1pc+power line package bag电源线包装袋1pc++base stand package bag底座包装袋2pc+remote control package bag遥控器包装袋1pc
Logistics & Warranty	
Container Loading(40HQC)	752
DMP formats	
Container Format	MKV
Video	.mpg,.mov,.mkv,.dat,.vob
Audio	.mp3,.m4a,.aac
Picture	.jpg,.jpeg, .bmp, .png