

# SH-DB1608

802.11n WiFi  
Self-Powered  
Smart Video  
Doorbell



Helping To Protect Your World



Easy Setup  
At Home



Apartments  
& Offices



Outbuildings  
& Lockups



Secure  
Access Areas

## Enabling Smart Technologies For Your Lifestyle

Waiting for that important delivery but you aren't at home? Want night and day security at your front door in all weathers?

The exciting Dynamode **SH-DB1608** is the latest IoT (Internet of Things) smart-home device that acts as your intelligent sentry for your home, apartment, office or even the garden shed!

Easy to install, without any wires courtesy of a long-life, built-in rechargeable battery, it lasts months on a full charge\* thanks to ULPC technology. Encased in a weatherproof, low profile design is a PIR motion detector, night-time viewing via IR detection and of course your regular doorbell button.

Fluid HD 720p video is assured via its multi-coated, wide angle (135 degrees) lens together with a unique, 2-way conversation system so you can talk and see your visitor from anywhere in the world on your smartphone.

## specifications:

Stylish, Slimline Video Doorbell with WiFi(tm)

**Smart 3000mAh Rechargeable Battery Technology**

ULPC Design lasts months on a single charge\*

**HD 720p, 1-Megapixel Colour CMOS Imaging System**

Multi-coated, optical lens, 1.2mm - 135-degree FoV

**Integral WiFi 802.11n/g/b with easy setup**

Night vision supported via IR detection

**Enabled, 2-way voice communications to the doorbell**

Weatherproof - Dimensions 6.7x2.3x12.5cm (WxDxH)

**PIR movement detection - Built-in 8Gb TF storage**

Easy, wire-free installation with tamper protection

**Free bundled apps for iOS(tm) and Android(tm)\*\***



\*Depends on usage, battery state  
\*\* Scan QR code on device



## Dynamode®

Copyright 2017 Dynamode  
All trademarks acknowledged E&OE.  
Details subject to change.V2.1