

CONTROL PRODUCTS

Piezo switches, Plastic, RGB LED Illuminated, 26mm


Plastic piezo switches offering rugged, sealed tamper and vandal proof solid state switching. Exceptional durability and reliability. Fitted with red, green and blue LED's for illumination.

- 26mm diameter actuator
- 22.5mm diameter mounting hole
- Normally open, momentary action
- Make impulse time of 125-300 msec
- Recessed face
- Wire termination
- IP68 Sealed
- Available in 12V and 24V LED's



CPS22IF-PLWH-12RGB



PART NO.	LED VOLTAGE
CPS22IF-PLWH-12RGB	12V DC
CPS22IF-PLWH-24RGB	24V DC



SPECIFICATIONS	
Operating voltage:	1-24V AC/DC
Switching current	0.2A max
Actuation force	3-5N
Operating temperature	20°C to +70°C
LED operating voltage	12V DC max OR 24V DC max
LED max current consumption:	(12V) (24V)
Red	18mA 18mA
Green	9mA 9mA
Blue	27mA 16mA
Ingress Protection	IP69
Lifetime	50 million operations
Material	POM



+44 (0)1638 716101
info@camdenboss.com
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 2



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS