























SELECTION CHART	1 	2 	3 	4 	6 
	COVER PLATES				
LOGIC PLUS	K3631WHI/GRA 10	K3632WHI/GRA 10	K3633WHI/GRA 10	K3634WHI/GRA 10	K3636WHI/GRA 1
METALCLAD PLUS	K3491ALM 10	K3492ALM 10	K3493ALM 5	K3494ALM 5	K3496ALM 1
ALBANY PLUS See Albany Plus Pg 173	K3431 1	K3432 1	K3433 1	K3434 1	K3436 1
EDGE See Edge Pg 124	K14331 1	K14332 1	K14333 1	K14334 1	K14346 1
ASPECT See Aspect Pg 90	K24331 1	K24332 1	K24333 1	K24334 1	K24346 1
ALLOY See Alloy Pg 152	K5331 1	K5332 1	K5333 1	K5334 1	
BOXES					
LOGIC PLUS flush	891ALM 10 2 x 20mm knockouts	891ALM 10 2 x 20mm knockouts	892ALM 5 4 x 20, 4 x 25mm knockouts	892ALM 5 4 x 20, 4 x 25mm knockouts	893ALM 5 4 x 20, 4 x 25mm knockouts
	821ALM 10 without knockouts	821ALM 10 without knockouts	822ALM 5 without knockouts	822ALM 5 without knockouts	823ALM 5 without knockouts
LOGIC PLUS surface metal	K2213ALM 5 5 x 20mm knockouts	K2213ALM 5 5 x 20mm knockouts	K2214ALM 5 7 x 20mm knockouts	K2214ALM 5 7 x 20mm knockouts	
	K2211ALM 5 without knockouts	K2211ALM 5 without knockouts	K2212ALM 5 without knockouts	K2212ALM 5 without knockouts	
LOGIC PLUS surface moulded	K2140WHI 10 with knockouts	K2140WHI 10 with knockouts	K2142WHI 5 with knockouts	K2142WHI 5 with knockouts	
LOGIC PLUS surface pvc	K2181WHI 10 with knockouts	K2181WHI 10 with knockouts	K2183WHI 5 with knockouts	K2183WHI 5 with knockouts	
METALCLAD PLUS & ALBANY PLUS surface	K8891ALM 10 5 x 20mm knockouts	K8891ALM 10 5 x 20mm knockouts	K8892ALM 5 7 x 20mm knockouts	K8892ALM 5 7 x 20mm knockouts	K8893ALM 5 4 x 20mm, 4 x 25mm knockouts
	K8821ALM 10 without knockouts	K8821ALM 10 without knockouts	K8822ALM 5 without knockouts	K8822ALM 5 without knockouts	K8823ALM 5 without knockouts
	K8901ALM 10 deep box 5 x 20mm knockouts	K8901ALM 10 deep box 5 x 20mm knockouts	K8902ALM 10 deep box 4 x 20mm, 4 x 25mm knockouts	K8902ALM 10 deep box 4 x 20mm, 4 x 25mm knockouts	
ALBANY PLUS ASPECT & EDGE	891ALM 10 2 x 20mm knockouts	891ALM 10 2 x 20mm knockouts	892ALM 5 4 x 20, 4 x 25mm knockouts	892ALM 5 4 x 20, 4 x 25mm knockouts	893ALM 5 4 x 20, 4 x 25mm knockouts
flush	821ALM 10 without knockouts	821ALM 10 without knockouts	822ALM 5 without knockouts	822ALM 5 without knockouts	823ALM 5 without knockouts
GRIDS					
Edge/Insignia & Aspect cover plates include an integral grid	K3701 10 	K3702 10 	K3703 10 	K3704 10 	K3703 X 2 10 












technical hotline +44 (0)1268 563720

modular | wiring devices

8 	9 	12 	18 	24 	Architrave 
K3638WHI/GRA 1 K3498ALM 1 K3438 1 K14348 1 K24348 1	 K3499ALM 1 K3439 1 K14349 1	K3639WHI 1 K3502ALM 1 K3442 1 K14352 1	 K3508ALM 1 K3448 1 K14358 1	 K3514ALM 1 K3454 1 K14354 1	 K3401 1 K14401 1
893ALM 5 4 x 20, 4 x 25mm knockouts 823ALM 5 without knockouts		895ALM 1 5 x 20, 5 x 25mm knockouts 825ALM 1 without knockouts			
K8893ALM 5 4 x 20mm, 4 x 25mm knockouts K8823ALM 5 without knockouts	K8895ALM 1 5 x 20mm, 5 x 25mm knockouts K8825ALM 1 without knockouts	K8895ALM 1 5 x 20mm, 5 x 25mm knockouts K8825ALM 1 without knockouts	K8898ALM 1 5 x 20mm, 5 x 25mm knockouts K8826ALM 1 without knockouts	K8900ALM 1 6 x 20mm, 6 x 25mm knockouts K8827ALM 1 without knockouts	
893ALM 5 4 x 20, 4 x 25mm knockouts 823ALM 5 without knockouts	895ALM 1 5 x 20, 5 x 25mm knockouts 825ALM 1 without knockouts	895ALM 1 5 x 20, 5 x 25mm knockouts 825ALM 1 without knockouts	898ALM 1 6 x 32mm knockouts	900ALM 1 6 x 32mm knockouts	3895ZIC 5 3 x 20mm knockouts (for flush mounting only) 3891ZIC 5 1 gang Architrave Boxes for EDGE
K3704 X 2 10 	K3703 X 3 10 	K3704 X 3 10 	K3706 X 3 10 	K3706 X 4 10 	K3708ZIC 10 

technical hotline +44 (0)1268 563720

modular | wiring devices

8 	9 	12 	18 	24 	Architrave 
K3638WHI/GRA 1 K3498ALM 1 K3438 1 K14348 1 K24348 1	 K3499ALM 1 K3439 1 K14349 1	K3639WHI 1 K3502ALM 1 K3442 1 K14352 1	 K3508ALM 1 K3448 1 K14358 1	 K3514ALM 1 K3454 1 K14354 1	 K3401 1 K14401 1
893ALM 5 4 x 20, 4 x 25mm knockouts 823ALM 5 without knockouts		895ALM 1 5 x 20, 5 x 25mm knockouts 825ALM 1 without knockouts			
K8893ALM 5 4 x 20mm, 4 x 25mm knockouts K8823ALM 5 without knockouts	K8895ALM 1 5 x 20mm, 5 x 25mm knockouts K8825ALM 1 without knockouts	K8895ALM 1 5 x 20mm, 5 x 25mm knockouts K8825ALM 1 without knockouts	K8898ALM 1 5 x 20mm, 5 x 25mm knockouts K8826ALM 1 without knockouts	K8900ALM 1 6 x 20mm, 6 x 25mm knockouts K8827ALM 1 without knockouts	
893ALM 5 4 x 20, 4 x 25mm knockouts 823ALM 5 without knockouts	895ALM 1 5 x 20, 5 x 25mm knockouts 825ALM 1 without knockouts	895ALM 1 5 x 20, 5 x 25mm knockouts 825ALM 1 without knockouts	898ALM 1 6 x 32mm knockouts	900ALM 1 6 x 32mm knockouts	3895ZIC 5 3 x 20mm knockouts (for flush mounting only) 3891ZIC 5 1 gang Architrave Boxes for EDGE
K3704 X 2 10 	K3703 X 3 10 	K3704 X 3 10 	K3706 X 3 10 	K3706 X 4 10 	K3708ZIC 10 