

# Rhino™ 4200



## Compact, Time-Saving Label Maker for On-The-Go Pros

- Familiar computer-style keyboard with country-specific layout for fast and easy text entry
- One-Touch “Hot Keys” provide shortcuts for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-length, general and breaker labels
- “Favorites” key provides single-key access to your most commonly used labels, symbols and terms
- Avoid repeated steps with the “Custom” key – customize and save settings for individual label formats
- Pre-programmed library with 150 symbols and terms for security, electrical, pro A/V, and facilities management
- Integrated rubber bumpers help prevent damage from accidental drops and falls
- Large back-lit display is easy to read, even in dimly-lit work areas
- Prints 57% faster than the competition\*

\*Based on independent testing of Rhino 4200 vs. Brother PT-1400 and Brother PT-7100 in default settings



### Single Unit Includes:

- Rhino 4200 Label Maker
- 12 mm White Vinyl Label Cartridge
- Quick Reference Guide



### Kit includes everything in single unit plus:

- Carry Case
- Rechargeable Battery
- AC Charging Adaptor



### Quick Specs

Unit Dimensions (H x W x L)	215 x 103 x 57 mm
Weight (excluding battery)	540 g
Mac®/PC Compatible	No
Accepts Label Sizes	6mm, 9mm, 12mm, 19mm
Tape Platform	IND Rhino™
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	15mm/sec
Barcodes	Yes, Code 39 & Code 128
Cutter Type	Manual
Batteries	6 AA or Rechargeable (not included)
AC Adapter	Yes (not included)
Networking	No
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price
S0955950	RHINO 4200 UK/IRL	Unit	8.8	15.6	23.0	0.7	1	3501170955956	
		Shelf	-	-	-	-	-	-	-
		Case	23.0	20.0	35.0	3.2	4	13501170955953	
		Pallet	120.0	80.0	120.0	216.3	240	-	
<b>Accessories</b>									
S0721430	RHINO AC Adapter	Unit	11.5	5.9	8.9	0.2	1	5411313400756	
S0895840	Rechargeable battery	Unit	8.5	3.2	8.9	0.1	1	3501170895849	
S0955950	KITCASE R4200 QWERTY UK/IRE	Unit	9.2	27.5	26.5	1.1	1	3501178529920	
		Shelf	-	-	-	-	-	-	-
		Case	29.0	28.0	29.0	3.8	3	13501170841393	
		Pallet	120.0	80.0	15.0	25.0	180	-	

# Rhino™ 4200 | Compatible Labels



## IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

## IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

## IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- For flat surfaces only
- Temperature rating: -40°C to 150°C

## IND Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.

- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: -55° C to 135°C

IND Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
<b>IND VINYL</b>													
9mm	5.5m	18443	-	-	-	-	-	1805437	-	-	-	-	-
12mm		18444	-	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412	
19mm		18445	-	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418	
<b>IND PERMANENT POLYESTER</b>													
6mm	5.5m	1805442	1805440	-	-	1805441	-	-	-	-	-	-	-
9mm		18482	18508DMO	-	-	18485	-	-	-	-	-	-	
12mm		18483	622289	-	-	18486	-	-	-	-	-	-	
19mm		18484	622290	-	-	18487	-	-	-	-	-	-	
<b>IND FLEXIBLE NYLON</b>													
12mm	3.5m	18488	-	18490	-	-	-	-	-	-	-	-	-
19mm	3.5m	18489	-	18491	-	-	-	-	-	-	-	-	-
<b>IND HEAT-SHRINK TUBE</b>													
6mm	1.5m	18051	-	18052	-	-	-	-	-	-	-	-	-
9mm		18053	-	18054	-	-	-	-	-	-	-	-	
12mm		18055	-	18056	-	-	-	-	-	-	-	-	
19mm		18057	-	18058	-	-	-	-	-	-	-	-	

Country of Origin: Belgium

**DISTRIBUTED BY:**  
Newell Europe Sàrl  
Chemin de Blandonnet 10  
1214 Vernier – Switzerland  
WWW.DYMO.COM

13-0103

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A Newell Rubbermaid Brand

©2014 Newell Europe LLC