



40-9526HDM

With a comprehensive line of RF connectors, we can provide a complete connectivity solution. We stock 50 and 75 ohm cables for Audio, Video and Data requirements, including hook-up cables for satellite and CATV installations; RCA cables and adapter cables for TV, DVD and VHS hookups; as well as BNC cables for networking and video applications. If not in stock in our warehouse, our custom cable department offers the capability to build any assembled or molded cable to your custom length or configuration, including BNC, 'N' UHF, Mini-UHF, TNC, SMA and 'F' versions.



Cable Type:	N/A
Crimp Tool:	24-312
Frequency Min:	0 GHz
Mounting Style:	Bulkhead Mount
ENDA ENDB Series:	N/A
Terminal Type:	Solder
Cable Length:	1 ft

Attenuation Accuracy:	26 AWG
Finish:	Copper
ENDB Series:	N/A
Gender Side 2:	N/A
ENDB Shape:	N/A
Terminal Style:	Receptacle
Colour:	Yellow
Frequency Max:	25 GHz
Average Power:	2 AWG
Gender Side 1:	N/A
Type:	Plug
Cable Group:	N/A
Body Material:	Plastic
Body Style:	Solder
Contact Plating:	Copper
Body Plating:	Copper
Impedance:	150 Ohm
Series Side 2:	N/A
Series Side 1:	N/A