

# HP Notebook 14-bw022na



Reliable performance. Beautiful design. Do more.

Power through your day with a stylish laptop created to keep you connected, and on top of everyday tasks. With reliable performance and long lasting battery life<sup>1</sup>—you can easily surf, stream and stay in touch with what matters most.



### The PC you can rely on

With the latest AMD<sup>2</sup> processors you are guaranteed the reliable performance you need to work and play. Enjoy long-lasting durability on a laptop designed to do what you want with ease.



### Connect with what matters

Stay entertained and keep connected with friends and family on a rich HD or on select models FHD display and HD<sup>3</sup> camera on select models. Plus, easily store and enjoy your favorite music, movies, and photos.



### Thoughtfully designed. Inside and out.

Beautifully designed inside and out this HP diagonal 35.6 cm (14") laptop is perfectly suited for your lifestyle. Playful patterns, unique textures and a chrome plated hinge (on select models) add a little color to your everyday.



<sup>1</sup> Battery life will vary depending on various factors including product model, configuration, loaded applications, features, use, wireless functionality, and power management settings. The maximum capacity of the battery will naturally decrease with time and usage. See <https://bapco.com/products/mobilemark-2014/> for details. <sup>2</sup> Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed. <sup>3</sup> Features may require software or other 3rd party applications to provide the described functionality.

# HP Notebook 14-bw022na



## Specifications

### Performance

**Operating System**

Windows 10 Home 64

**Processor**

AMD Dual-Core A4-9120 APU (2.2 GHz base frequency, up to 2.5 GHz burst frequency, 1 MB cache)<sup>6,7</sup>

Processor family: AMD Dual-Core A-Series processor

**Memory**

4 GB DDR4-1866 SDRAM (1 x 4 GB)

Transfer rates up to 1866 MT/s

**Storage**

1 TB 5400 rpm SATA

Dropbox<sup>1</sup>

**Graphics**

Integrated AMD Radeon™ R3 Graphics

**Audio**

Dual speakers

**Display**

35.6 cm (14") diagonal HD SVA anti-glare WLED-backlit (1366 x 768)

**Power**

45 W AC power adapter

**Battery Type**

4-cell, 41 Wh Li-ion

User-replaceable battery

Supports battery fast charge: approximately 90% in 90 minutes<sup>5</sup>

**Target battery life**

Up to 10 hours and 30 minutes estimated battery time<sup>3</sup>

### Connectivity

**Network interface**

Integrated 10/100/1000 GbE LAN

**Wireless connectivity**

802.11b/g/n (1x1) Wi-Fi® and Bluetooth® 4.2 combo (Miracast compatible)

**Ports**

2 USB 3.1 Gen 1 (Data transfer only); 1 USB 2.0; 1 HDMI; 1 VGA; 1 RJ-45; 1 headphone/microphone combo

1 multi-format SD media card reader

**Webcam**

HP Webcam with integrated digital microphone

### Design

**Product Color**

Jet black; Woven texture pattern

### Software

**HP Apps**

HP Audio Switch; HP JumpStart; HP Sure Connect; HP CoolSense; HP Orbit

**Software**

Netflix; 1 month trial for new Microsoft® Office 365 customers

**Service & support**

McAfee LiveSafe™<sup>2</sup>

### Additional information

**Part Number**

P/N: ZWF97EA #ABU

UPC/EAN code: 192018351226

**Energy Efficiency Compliance**

ENERGY STAR® certified; EPEAT® Silver registered

**Weight**

1.9 kg

**Dimensions**

34 x 24 x 2.37 cm

**Warranty**

1 year limited parts, labour, and pickup and return service; You can expand the warranty coverage of your product to reach up to 3 years in total; for more information go to the "Options and accessories" web section on hp.com product pages.

**Keyboard**

Full-size island-style keyboard

Touchpad with multi-touch gesture support

**Security management**

Kensington MicroSaver® lock slot

## Compatible accessories\*

\* Not included.

## Warranty services\*



**3-year pickup and return**  
U1P53E

**HP Smart Friend 1 Month SVC**  
HG382E

<sup>1</sup> 25 GB of free online storage for one year from date of registration. For complete details and terms of use, including cancellation policies, visit the website at [www.dropbox.com](http://www.dropbox.com). Internet service required and not included.<sup>2</sup> McAfee LiveSafe 30-day free trial offer (Internet access required. First 30 days included. Subscription required for live updates afterwards.)<sup>3</sup> Estimated Windows 10 battery life based on Windows 10 / MobileMark® 2014 benchmarking. Battery life will vary depending on various factors including product model, configuration, loaded applications, features, use, wireless functionality, and power management settings. The maximum capacity of the battery will naturally decrease with time and usage. See [www.bapco.com](http://www.bapco.com) for additional details.<sup>5</sup> Recharges your battery up to 90% within 90 minutes when the system is off (using "shut down" command). Recommended for use with the HP adapter provided with the notebook, not recommended with a smaller capacity battery charger. After charging has reached 90% capacity, charging speed will return to normal speed. Charging time may vary +/-10% due to System tolerance. Available on select HP Spectre, HP Envy, HP Omen and HP Pavilion PC models. See <http://store.hp.com> for a full list of product features.<sup>6</sup> Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed. AMD and Radeon are trademarks of Advanced Micro Devices, Inc.<sup>7</sup> Burst frequency performance varies depending on hardware, software and overall system configuration.

