

2 Port HDMI Video Splitter with Audio - USB Powered

Product ID: ST122HDMILE



The ST122HDMILE 2-Port HDMI® Video Splitter with Audio lets you share a single high definition video and audio source between two HDMI or DVI (with HDMI to DVI cable) displays. The HDMI splitter is USB-powered, making it ideal for use with desktop and laptop computers that offer HDMI output.

The USB powered High Speed HDMI splitter is HDCP 1.1 compliant, delivering outstanding audio capability and flawless digital video at resolutions of up to 1080p.

To overcome connection distance limitations, the HDMI splitter also functions as an HDMI distribution amplifier allowing you to situate HDMI monitors up to 45ft (15m) away from the HDMI source - a perfect solution for connecting an HDMI-capable computer to monitors, projectors or plasma screens as needed.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connecting multiple HDMI® enabled projectors, LCD Displays, and Plasma Displays from a single PC source
- Ideal for classroom settings, where educators can display their computer screen on multiple displays for better visibility
- Perfect for corporate boardrooms that employ multiple screens or projectors
- Set up your trade show display with multiple screens
- Use in retail environments for advertising or training

Features

- Splits an HDMI® source to 2 outputs, without signal loss
- Integrated signal amplifier - situate displays up to 45ft(15m) away
- Supports a wide range of HDTV resolutions, from 480p to 1080p
- USB-powered - no wall outlet or bulky power supply required
- High Speed HDMI® and HDCP 1.1 compliant
- Compact design

| | | |
|-------------------------------------|-------------------------------|--|
| Hardware | Warranty | 2 Years |
| | Daisy-Chain | Yes |
| | Industry Standards | High Speed HDMI®, HDCP |
| | Ports | 2 |
| Performance | Maximum Cable Length | 15 m [49.2 ft] |
| | Supported Resolutions | 480p, 480i, 720p, 1080i, 1080p 1600x1200(UXGA) |
| | Wide Screen Supported | Yes |
| Connector(s) | Connector A | 1 - HDMI (19 pin) Male 1 - USB Type-A (4 pin) USB 2.0 Male |
| | Connector B | 2 - HDMI (19 pin) Female |
| Special Notes / Requirements | System and Cable Requirements | An HDMI source (desktop / laptop) with a USB port for powering ST122LE. |
| Indicators | LED Indicators | 1 - Power |
| Power | Input Current | 500mA |
| | Input Voltage | 5 DC |
| | Power Source | USB-Powered |
| Environmental | Humidity | 0~95% RH |
| | Operating Temperature | 0°C to 70°C (32°F to 158°F) |
| | Storage Temperature | -20°C to 85°C (-4°F to 185°F) |
| Physical Characteristics | Cable Length | 280 mm [11 in] |
| | Color | Black |
| | Enclosure Type | Plastic |
| | Product Height | 25 mm [1 in] |
| | Product Length | 75 mm [3 in] |
| | Product Weight | 80 g [2.8 oz] |
| | Product Width | 53 mm [2.1 in] |
| Packaging Information | Shipping (Package) Weight | 0.2 kg [0.4 lb] |
| What's in the Box | Included in Package | 1 - HDMI Splitter 1 - 24" USB Power cable 1 - Instruction Manual |

Product appearance and specifications are subject to change without notice.