

LOGO! TD Text Display, 6-line, 3 background colors, 2 Ethernet ports, installation accessories for LOGO! 8



Figure similar

General information	
Product type designation	LOGO! TDE
Suitability for use	Can be used with LOGO! 8 and higher
Display	
Design of display	FSTN
Line display	
<ul style="list-style-type: none"> <li>• Number of lines</li> </ul>	6
<ul style="list-style-type: none"> <li>• Number of characters per line</li> </ul>	20
Backlighting	
<ul style="list-style-type: none"> <li>• Type of backlighting</li> </ul>	LED
Control elements	
Keyboard fonts	
<ul style="list-style-type: none"> <li>• System keys</li> </ul>	Yes
<ul style="list-style-type: none"> <li> <ul style="list-style-type: none"> <li>— Number of configurable system keys</li> </ul> </li> </ul>	0
<ul style="list-style-type: none"> <li>• alphanumeric keyboard</li> </ul>	No
Installation type/mounting	

Wall mounting/direct mounting	No
<b>Supply voltage</b>	
Type of supply voltage	AC/DC
Rated value (DC)	12 V; 12/24 V DC, 24 V AC
<b>Power loss</b>	
Power loss, typ.	1.8 W; At 24 V DC
<b>Interrupts/diagnostics/status information</b>	
Diagnostic functions	No
<b>Degree and class of protection</b>	
IP (at the front)	IP65
<b>Standards, approvals, certificates</b>	
CE mark	Yes
UL approval	Yes
FM approval	Yes
KC approval	Yes
Marine approval	
• American Bureau of Shipping (ABS)	Yes
<b>Ambient conditions</b>	
Ambient temperature during operation	
• min.	-20 °C; No condensation
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)
<b>Configuration</b>	
Configuration software	
• Configuration tool	LOGO! Soft Comfort V8
<b>Accessories</b>	
belongs to product	LOGO!
<b>Mechanics/material</b>	
Design of housing	plastic
<b>Dimensions</b>	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Overall depth	38.7 mm

## Weights

Weight, approx.	220 g
-----------------	-------

## Scope of supply

Delivery quantity in pieces	1
-----------------------------	---

<b>last modified:</b>	02/10/2018
-----------------------	------------