

CT4026

18 kV High Voltage Probe



Overview:

The Elditest CT4026 is a 18 kV high voltage divider probe for use with both digital and analog oscilloscopes.

Features:

- Input voltage of 18 kV (DC+ACpk)
- 150 MHz bandwidth
- Voltage dividing of 1000:1
- Frequency compensation

Technical data subject to change.
© Cal Test Electronics 2017.

caltestelectronics.com

Datasheet

Specifications	
Operating Parameters	
Maximum Input Voltage (CAT I)	18 kV (DC + ACpk) 12 kVrms AC
Maximum Loading Current	90 μ A
Division Ratio	1000:1
Bandwidth	DC to 150 MHz
Compensation Range	10 pF to 35 pF
Temperature Coefficient	\leq 200 ppm/ $^{\circ}$ C
Input Resistance	200 M Ω
Input Capacitance	1.5 pF
Rise Time	2.4 ns
Signal/Noise	>60 dB @ 1 KHz >50 dB @1 MHz
Accuracy	
DC Volts	\leq 3%
AC Volts	\leq 3% at 1 kHz
General	
Cable Length	6.6 ft (2 m)
Designed for Use in	Pollution Degree 2
Operating Environment	14 $^{\circ}$ F to 131 $^{\circ}$ F (-10 $^{\circ}$ C to 55 $^{\circ}$ C)
Storage Temperature	-4 $^{\circ}$ F to 158 $^{\circ}$ F (-20 $^{\circ}$ C to 70 $^{\circ}$ C)
Humidity	\leq 85% relative humidity at 95 $^{\circ}$ F (35 $^{\circ}$ C)
Dimensions	3.1 x 3.1 x 12.6 in (8 x 8 x 32 cm)
Weight	1.0 lbs (460 g)
Warranty	One-year warranty