


DESTB-0253

3 Pole steatite ceramic high temperature blocks terminal 32a 450v


SPECIFICATION

| | |
|-----------------------------------|--|
| Number of Poles | 3 |
| Body Material | Steatite |
| Colour | White |
| Min Conductor Size (Sq mm) | 1.5 |
| Max Conductor Size (Sq mm) | 6 |
| Min Conductor Size AWG | 22 |
| Max Conductor Size AWG | 12 |
| Max Current (A) | 32 |
| Max Voltage (V) | 450 |
| Minimum Temp Rating °C | -40 |
| Max Temp Rating °C | 300-350 |
| Pitch (mm) | 11 |
| Height (mm) | 15.6 |
| Width (mm) | 18 |
| Length (mm) | 32 |
| Comments | M3 conductor clamping screws, maximum torque=0.5Nm |