

PRODUCT SPECIFICATION

EN#: 4710810383823

SD-205

62Pcs Security Bits Set



Safety and environmental protection:

- RoHS & Pb free: Pb free

Physical and function:

- Torque (kgf-cm): 500±

Handle:

- Material of handle: PP, TPR
- Handle O.D. (mm): 38.4

Blade:

- Material of blade: CRV 50BV30
- Color of blade: Primary colors
- Blade hardening: Quench hardening process
- Shape of blade: Round head
- Magnetic tips: Non

Bits:

- 延長桿_規格內容

公頭規格(單位: 英吋)	母頭外徑 D1 (mm)	鐵桿外徑 D2 (mm)	全長 L (mm)	材質打 印	PK LOGO 打印	球型雙用 設計	快拆裝 置	滾珠裝 置	Joints binding mode
1/4"	10	6.3	60	Non	Non	Non	Non	Non	Non

- 棘輪手柄_規格內容




The first type symbol	Surface Finish	Length (mm)	Specifications Print	Material Print	PK LOGO	Angle and teeth	Ratchet direction switch	Quick release device	Joints binding mode
 Nut	Satin finish	190	Non	Non	Non	Non	Yes	Non	Magnet

- Torx

The first type symbol	Head Specifications	六角對邊尺寸	Surface Finish	Bit Length (mm)	Color	規格打印	材質打印
 Torx tamper proof	T5H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T6H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T7H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T8H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T9H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T10H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T15H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T20H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T25H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T27H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T30H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Torx tamper proof	T40H	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non

- specification contents

The first type symbol	Head Specifications	六角對邊尺寸	Surface Finish	Bit Length (mm)	本體色環	規格打印	材質打印
 Slotted	SL 1/8"	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Slotted	SL 3/16"	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Phillips	PH0	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Phillips	PH1	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Phillips	PH2	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non

 Pozidriv	PZ0	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Pozidriv	PZ1	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non
 Pozidriv	PZ2	6.35mm (1/4")	Sand blasting	25	Non	Yes	Non

Product Weight (w/o package):

Weight(g)	Measurement		
	L(mm)	W(mm)	H(mm)
670	275	79.7	43.6

Individual Packing

- Packing: Plastic Box & Shink Parking

Master Packing:

	Pieces	N.W. (Kg)	G.W. (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.67	27.7	7.9	4.3	-
Inner Box	6	4.02	4.13	28	16.5	13.5	0.22
CTN	12	8.04	8.75	34	30	16	0.58