

CAT 6A FLEXIBLE S/FTP TOURCAT RJ45 LEADS



- Van Damme Cat 6A Flexible S/FTP Tourcat cable terminated with Van Damme Cat 6A shielded RJ45 connectors
- For Gigabit and 10G network signals
- Rugged, flexible assembly ideal for tactical use
- Hand terminated in the UK and individually tested for performance
- RoHS Compliant

COMPONENT PARTS

Van Damme Cat 6A Flexible S/FTP Tourcat cable

- Flexible PVC jacketed 26AWG stranded cable with individually screened pairs and a 75% coverage overall braided screen
- Meets the requirements of Category 6_A TIA/EIA-568-C-2 and ISO/IEC 11801 Class E_A
- Suitable for Gigabit and 100 Mbit to a maximum channel link distance of 75 metres
- Suitable for 10G Cat 6_A to a maximum channel link distance of 60 metres
- Cable performance tested using a Fluke DTX cable verifier

Van Damme Cat 6A RJ45 connectors

- High quality shielded Cat 6_A RJ45 connector with polycarbonate body and copper alloy shielding
- 50 µm gold plated contacts
- Integral load bar for improved crosstalk performance

PRODUCT LISTING

Part No.	Length
401-466-001	1m
401-466-002	2m
401-466-003	3m
401-466-005	5m
401-466-010	10m
401-466-015	15m
401-466-020	20m