

## Basic

Brand Name: Lenovo  
Form Factor: Tower  
Keyboard Localization: English (UK)  
Operating System Architecture: 64-bit  
Operating System Language: English  
Operating System Platform: Windows  
Operating System: Windows 10 Pro  
Optical Drive Type: DVD-Writer  
Processor Manufacturer: Intel  
Processor Model: i3-7100  
Processor Speed: 3.90 GHz  
Processor Type: Core i3  
Product Family: V520-15IKL  
Product Type: Desktop Computer  
Standard Memory: 4 GB  
Total Solid State Drive Capacity: 256 GB

## General Information

Brand Name: Lenovo  
Manufacturer Part Number: 10NK006QUK  
Manufacturer Website Address: <http://www.lenovo.com/uk/en/>  
Manufacturer: Lenovo Group Limited  
Product Model: 10NK006QUK  
Product Name: V520-15IKL 10NK006QUK Desktop Computer  
Product Series: V520-15IKL  
Product Type: Desktop Computer

## Input Devices

Keyboard Localization: English (UK)

## Memory

Memory Technology: DDR4 SDRAM  
Standard Memory: 4 GB

## Miscellaneous

Package Contents:

- V520-15IKL 10NK006QUK Desktop Computer
- Keyboard
- Mouse

## Physical Characteristics

Form Factor: Tower

## Power Description

Input Voltage: 120 V AC  
230 V AC

## Processor & Chipset

Processor Generation: 7th Gen  
Processor Manufacturer: Intel  
Processor Model: i3-7100  
Processor Speed: 3.90 GHz  
Processor Type: Core i3

## Software

Operating System Architecture: 64-bit  
Operating System Platform: Windows  
Operating System: Windows 10 Pro

## Storage

Optical Drive Type: DVD-Writer  
Total Solid State Drive Capacity: 256 GB

## Warranty

Limited Warranty: 1 Year