

Basic

Brand Name: Lenovo
Form Factor: Small Form Factor
Keyboard Localization: English (UK)
Operating System Architecture: 64-bit
Operating System Language: English
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-7100
Processor Speed: 3.90 GHz
Processor Type: Core i3
Product Family: ThinkCentre M710s
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Hard Drive Capacity: 500 GB

General Information

Brand Name: Lenovo
Manufacturer Part Number: 10M70051UK
Manufacturer Website Address: <http://www.lenovo.com/uk/en/>
Manufacturer: Lenovo Group Limited
Product Line: ThinkCentre
Product Model: 10M70051UK
Product Name: ThinkCentre M710s 10M70051UK Desktop Computer
Product Series: M710s
Product Type: Desktop Computer

Input Devices

Keyboard Localization: English (UK)

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Package Contents:

- ThinkCentre M710s 10M70051UK Desktop Computer
- Keyboard
- Mouse

Physical Characteristics

Form Factor: Small Form Factor

Power Description

Input Voltage: 120 V AC

Processor & Chipset

Processor Generation: 7th Gen
Processor Manufacturer: Intel
Processor Model: i3-7100
Processor Speed: 3.90 GHz
Processor Type: Core i3

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro

Storage

Optical Drive Type: DVD-Writer
Total Hard Drive Capacity: 500 GB

Warranty

Limited Warranty: 3 Year