

Product information

Twin 18v LXT Slide Compound Mitre Saw



Satisfying the professional's needs

DLS714Z

Battery Type	Lithium-ion
Voltage	36 (18x2) v
Body only machine	1
Blade Diameter	190 mm
Bore Diameter	20 mm
No Load Speed	5700 rpm
Max bevel range	45 - 5 °
Max mitre range	47 - 57 °
Max Cutting Capacity	52 x 300 mm
Noise sound pressure	88 dB(A)
Noise sound power	97 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	13.5 kg



STANDARD EQUIPMENT: TCT saw blade, Dust bag, Holder set, Hex wrench, Vertical vice, Triangular rule

- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Brushless motor
- Double Sliding Mechanism
- Soft start
- Easy to Grip handle with anti-slip elastomer surface
- LED indicator panel for battery fuel and indication of automatic speed control
- Electric brake
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.
- Cuts up to 300mm in a single pass

Details correct as of: 1-3-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com