

71 31 250

KNIPEX CoBolt® XL Compact Bolt Cutters



- For powerful cutting of larger cross-sections as well as very hard materials
- Two-hand operation for maximum cutting force
- 60 % less effort required compared to high leverage diagonal cutters of the same size
- 40-fold increase of manual force due to special joint design
- With gripping surface below the joint for gripping and pulling wires with a diameter as from 1.0 mm
- Induction-hardened precision blades: cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- Blades with recess for easier cutting of larger cross-sections thanks to better leverage close to the fulcrum

Article No.	71 31 250
EAN	4003773079644
Pliers	black atramentized
Handles	plastic coated
Cutting capacities medium hard wire (diameter) Ø mm	6,0
Cutting capacities hard wire (diameter) Ø mm	4,3
Cutting capacities piano wire (diameter) Ø mm	4,2
Length mm	250
Net weight g	465

technical change and errors excepted