

34 12 130

Precision Electronics Gripping Pliers





- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Smoothly ground gripping surfaces, edges finely rounded
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened
 - Style: flat, wide jaws

The subtle difference

KNIPEX precision electronics pliers are made of high-quality ball bearing steel and processed with the highest degree of care. Each opening movement is gentle and even without backlash. Each work step proceeds reliably and precisely. This makes work much easier for professionals.

Article No.	34 12 130
EAN	4003773061458
Pliers	burnished
Head	polished
Handles	with multi-component grips
Style	1
B mm	21,9
D mm	6,5
E mm	1,4
F mm	3,5
A mm	11,2
Nominal size	130 mm
Length mm	135
Net weight g	61



technical change and errors excepted

