


13 01 160




Electricians' Pliers




- The ideal pliers for cable work
- For gripping and bending wire
- For cutting medium hard and hard wire
- Precision cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- With precision stripping holes
- For crimping end sleeves (ferrules)
- Vanadium electric steel, forged, multi stage oil-hardened



Article No.	13 01 160
EAN	4003773034971
Head	polished
Handles	plastic coated
Pliers	black atramentized
Cutting capacities medium hard wire (diameter) Ø mm	2,5
Cutting capacities hard wire (diameter) Ø mm	1,6
Stripping capacities in square millimetres mm²	0,5 - 0,75 / 1,5 / 2,5
Length mm	160
Net weight g	112



Gripping




Cutting



Stripping

technical change and errors excepted



Crimping 0.5 to 2.5 mm²