

97 52 38

KNIPEX PreciForce® Crimping Pliers



- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



For daily crimping applications, the specialist likes crimping pliers that work precisely and reliably. In addition, they should be light, comfortable to use, robust and reasonably priced: PreciForce®.

Article No.	97 52 38
EAN	4003773051909
Pliers	burnished
Handles	with multi-component grips
Applications	insulated and non-insulated end sleeves (ferrules)
Capacity in square millimetres mm²	0,25 - 6,0
Number of crimping positions	5
AWG	23 - 10
Length mm	220
Net weight g	493

technical change and errors excepted

