

# 97 52 35

## KNIPEX PreciForce® Crimping Pliers



- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



For daily crimping applications, the specialist likes crimping pliers that work precisely and reliably. In addition, they should be light, comfortable to use, robust and reasonably priced: PreciForce®.

<b>Article No.</b>	97 52 35
<b>EAN</b>	4003773051886
<b>Pliers</b>	burnished
<b>Handles</b>	with multi-component grips
<b>Applications</b>	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,5 - 6,0
<b>Number of crimping positions</b>	3
<b>AWG</b>	20 - 10
<b>Length mm</b>	220
<b>Net weight g</b>	494

*technical change and errors excepted*



### Spare Parts

<b>Article No.</b>	<b>EAN</b>	
97 59 20	4003773053934	Extension spring for 97 52 xx
97 59 21	4003773053941	Extension spring for 97 52 xx