

97 52 34

KNIPEX PreciForce® Crimping Pliers



- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



For daily crimping applications, the specialist likes crimping pliers that work precisely and reliably. In addition, they should be light, comfortable to use, robust and reasonably priced: PreciForce®.

Article No.	97 52 34
EAN	4003773051879
Pliers	burnished
Handles	with multi-component grips
Applications	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres mm²	0,1 - 2,5
Number of crimping positions	4
AWG	27 - 13
Length mm	220
Net weight g	483

technical change and errors excepted



Spare Parts

Article No.	EAN	
97 59 20	4003773053934	Extension spring for 97 52 xx
97 59 21	4003773053941	Extension spring for 97 52 xx