

# 95 32 315 A

## Cable Cutter (ratchet action) for steel wire armoured cables (SWA cable)




- Cuts through steel wire armoured cables with a diameter of up to 45 mm / 380 mm<sup>2</sup> (e.g. 4 x 95 mm<sup>2</sup>) using one or two-handed operation
- Sturdy. Easy to use. Stable.
- Simple handling due to low weight (800 g) and compact design (315 mm length) – can also be used in confined areas
- Precision ground blades and induction hardened cutting edges cut smoothly and neatly without crushing
- Innovative high leverage three-stage ratchet-drive
- Support area for putting down the pliers when cutting
- Not suitable for cutting ACSR cable and wire rope!
- High-grade special tool steel, forged, multi stage oil-hardened




<b>Article No.</b>	95 32 315 A
<b>EAN</b>	4003773078562
<b>Tool</b>	black lacquered
<b>Handles</b>	with multi-component grips
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	45
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	380
<b>MCM</b>	750
<b>AWG</b>	
<b>Length mm</b>	315
<b>Net weight g</b>	800



Precision milled and induction hardened cutting edge



Cross-section of a steel wire armoured cable



Cross-section of a steel wire armoured cable

technical change and errors excepted

### Accessories

Article No.	EAN	
95 39 315 A01	4003773078586	Pivot cutter repair kit for 95 32 315 A and 95 36 315 A (ratchet action)
95 39 315 A02	4003773078593	Fixed cutter repair kit for 95 32 315 A and 95 36 315 A (ratchet action)