

64 22 115

Electronics End Cutting Nipper



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- High-grade special tool steel, forged, multi stage oil-hardened
 - Style:End Cutter, mini-blade with small bevel



Article No.	64 22 115
EAN	4003773017806
Head	mirror polished
Handles	with multi-component grips
Style	2
Cutting capacities soft wire (diameter) Ø mm	0,8
B mm	20,0
D mm	6,0
C mm	3,0
A mm	10,0
Length mm	115
Net weight g	65

technical change and errors excepted

