

# 97 71 180

## Crimping Pliers for end sleeves (ferrules)



- Also as VDE version
- Easy crimping due to optimised transmission ratio
- Light and slim design
- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm<sup>2</sup>
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened



|  |                        |
|--|------------------------|
| <b>Article No.</b>                                   | 97 71 180              |
| <b>EAN</b>   | 4003773040668          |
| <b>Head</b>  | polished               |
| <b>Handles</b>                                       | plastic coated         |
| <b>Applications</b>                                  | End Sleeves (ferrules) |
| <b>Capacity in square millimetres mm<sup>2</sup></b> | 0,25 - 16,0            |
| <b>Number of crimping positions</b>                  | 9                      |
| <b>AWG</b>   | 23 - 5                 |
| <b>Length mm</b>                                     | 180                    |
| <b>Net weight g</b>                                  | 205                    |



*technical change and errors excepted*

