


## P2757

### Replaceable Probe

Product Family: Pylon



#### Mechanical:

**Test Center (mil):** 187

**Test Center (mm):** 4.75

**Overall Length (mil):** 1,210

**Overall Length (mm):** 30.73

**Overall Length Remark:** Tip 2C: 1140 mil (28.96 mm)

Tip 1W: 1205 mil (30.61 mm) Tip 2W: 1205 mil (30.61 mm)

**Full Travel (mil):** 230

**Full Travel (mm):** 5.84

**Recommended Travel (mil):** 167

**Recommended Travel (mm):** 4.24

#### Thermal:

**Max Operating Temp (°C):** 150

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 20

**Average DC Resistance lower than (mOhm):** 10

#### Materials & Finishes:

**Plunger Material:** Heat-treated BeCu, Gold plated over hard Nickel

**Barrel Material:** Phosphor Bronze, Gold plated

**Ball Material:** Stainless Steel

#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

#### Spring Material

Standard - 2.00 (57.00) - 4.00 (113.00) - Stainless Steel

Alternate - 3.50 (99.00) - 6.85 (194.00) - Stainless Steel

#### Body Type

Straight


Pylon Bend

## TIPS:


Tip Materials: BeCu, Gold plated

Tips:


P2757-1C




P2757-1R




P2757-1V



P2757-1W



P2757-2W




P2757-3W




## Related Products:

S2757-2ED



S2757-2ETD



S2757-2EWWD

