


XZCP0166L2

pre-wired connectors XZ - straight female - Ø 8 mm - 3 pins - cable PUR 2m



Main

| | |
|------------------------------------|----------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / separate part type | Pre-wired connectors |
| Series name | General purpose |

Complementary

| | |
|--------------------------------|--|
| Electrical connection | Ø 8 mm, 3 pins straight female connector |
| Cable connector fixing | Clip-on |
| Status LED | Without |
| Cable length | 2 m |
| Cable outer diameter | 5.2 mm |
| Cable composition | 3 x 0.34 mm ² |
| Wire insulation material | PUR |
| [Ue] rated operational voltage | 60 V AC 75 V DC |

| | |
|-----------------------|-----------|
| [In] rated current | 4 A |
| Contact resistance | 5000 µOhm |
| Insulating resistance | 1 GΩ |
| Product weight | 0.05 kg |


Environment

| | |
|---------------------------------------|--|
| IP degree of protection | IP65 IP67 |
| Product certifications | CULus |
| Ambient air temperature for operation | -40...80 °C (static) -5...80 °C (flexing) |
| Ambient air temperature for storage | -40...80 °C |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0649 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available Download Product Environmental |
| Product end of life instructions | Available Download End Of Life Manual |


Dimensions



L : Length of cable

Connections and Schemes

Connector



BU : Blue
BN : Brown
BK : Black