



Main

| | |
|------------------------------------|----------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / separate part type | Pre-wired connectors |

Complementary

| | |
|--------------------------------|--|
| Electrical connection | M12, 5 pins (included earth pin) straight female connector |
| Cable connector fixing | Screw-on |
| Collar material | Metal |
| Status LED | Without |
| Cable length | 25 m |
| Cable outer diameter | 5.9 mm |
| Cable composition | 5 x 0.34 mm ² |
| Wire insulation material | PUR |
| [Ue] rated operational voltage | 30 V AC 36 V DC |
| [In] rated current | 4 A |
| Contact resistance | <= 5000 µOhm |
| Insulating resistance | >= 1 GΩ |

Environment

| | |
|---------------------------------------|--|
| IP degree of protection | IP65 IP67 IP69K |
| Product certifications | CULus |
| Ambient air temperature for operation | -40...80 °C (static) -5...80 °C (flexing) |
| Ambient air temperature for storage | -40...80 °C |

Offer Sustainability

| | |
|--------------------------|---------------------------|
| Sustainable offer status | Not Green Premium product |
|--------------------------|---------------------------|