

SylStick

SYLSTICK WHITE WITH SENSOR BATTERY POWERED

0053271



Product features

- Battery operated linear light with sensor for various applications where no electrical socket is available. Pearl white finish. Ideal for closets, drawers, stairs, corridors, and bathrooms or it can be used as a reading or torch light. Sensor detection range is 3m with 120°. Delightful uniform diffused light. Vertical and horizontal tiltable in 3 positions. Easy to install with self-adhesive tape or screws. 3xAAA Batteries required and last 4 hours at 'on' mode. Neutral white 4000K colour temperature.

PRODUCT OVERVIEW

Certifications	CE
Colour temperature (K)	4000
Colour	Pearl White
EAN code	5410288532714
Housing	Polycarbonate
IP rating	IP20
Light colour	Neutral white
Mount	Surface Mounted
Ordering number	0053271
Technology	LED
Voltage (V)	4.5

DATA TABLE

General data

Certifications	CE
EAN code	5410288532714
General application	Residential & Consumer
Housing	Polycarbonate
Mount	Surface Mounted
Ordering number	0053271
Product name	SYLSTICK WHITE WITH SENSOR BATTERY POWERED
Technology	LED

Product features

Battery operated linear light with sensor for various applications where no electrical socket is available. Pearl white finish. Ideal for closets, drawers, stairs, corridors, and bathrooms or it can be used as a reading or torch light. Sensor detection range is 3m with 120°. Delightful uniform diffused light. Vertical and horizontal tiltable in 3 positions. Easy to install with self-adhesive tape or screws. 3xAAA Batteries required and last 4 hours at 'on' mode. Neutral white 4000K colour temperature.

SylStick

SYLSTICK WHITE WITH SENSOR BATTERY POWERED

0053271

Optical data

Colour temperature (K)	4000
Light colour	Neutral white

Physical data

Colour	Pearl White
Height (mm)	31
IP rating	IP20
Length (mm)	180
Width (mm)	27

Electrical data

Electrical protection	CLASS III
Total power consumption (W)	0.25
Voltage (V)	4.5

TECHNICAL DRAWINGS

