

ToLEDo Retro A60

ToLEDo RT A60 470LM E27 SL

0027160



Product features

-



PRODUCT OVERVIEW

Lamp finish	Clear
Lamp shape	GLS
Colour temperature (K)	2700
CRI (Ra)	80
Dimmable	No
EAN code	5410288271606
Energy class	A++
Equivalent watt (W)	40
Cap/Base	E27
Type	ToLEDo Retro A60
Watt (Nominal) (W)	4
Light colour	Homelight
Ordering number	0027160
Efficacy (Rated) (lm/w)	117.5
Average life (h) - L70/B50	15000
Luminous flux (Rated) (lm)	470
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (h) at Ta 25° C	15000
Control gear required	No
Lamp finish	Clear
Lamp shape	GLS
Dimmable	No

ToLEDo Retro A60

ToLEDo RT A60 470LM E27 SL

0027160

Dry applications use only	Yes
EAN code	5410288271606
Energy class	A++
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	E27
Lamp mercury content (mg)	0
Type	ToLEDo Retro A60
No. of switching cycles before premature failure (min)	>50,000
Optimal operating condition (°C)	25
Ordering number	0027160
Product name	ToLEDo RT A60 470LM E27 SL
Average life (h) - L70/B50	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
E-number SE	8290503
E-number FI	4740283

Optical data

Colour temperature (K)	2700
CRI (Ra)	80
Light colour	Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	470
Luminous flux (Rated) (lm)	470
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Current (A)	38
Drive current (mA)	38
Equivalent watt (W)	40
kWh per 1000 hours burning time	4
Lamp power factor	0.5
Watt (Nominal) (W)	4
Efficacy (Rated) (lm/w)	117.5

ToLEDo Retro A60

ToLEDo RT A60 470LM E27 SL

0027160

Watt (Rated) (W)	4
Voltage (V)	220-240

Physical data

Max. Lamp Diameter (mm) - D	60
Lamp Length (mm) - C/L	105
Lamp dimension equal to filament lamp equivalent	Yes

