

## ToLEDo Retro Candle

ToLEDo RT Candle 250LM B22 SL

0027182



### Range Features

- LED Chip technology using a virtual filament design which creates a warm ambiance similar to traditional lamps
- First lamp of its type to achieve A++ rating - up to 134 lm/W
- Suitable for replacement of up to 60W incandescent lamps
- Available in clear and satin versions
- Packed in individual boxes (SL) or in blisters (BL)
- Up to 90% energy saving compared to incandescent lamps
- Cooler burning versus standard LED lamps
- Dimensional compatibility with all fixtures
- Average lifetime from 6000 hours up to 15 000 hours
- 3 years warranty
- WARNING : If the outer glass jacket is broken conductive parts may still be active. Lamps must not be touched before making sure the mains cable is not live. Switch off the main electrical supply before replacing lamp!
- 

## PRODUCT OVERVIEW

Lamp finish	Clear
Lamp shape	Candle
Colour temperature (K)	2700
Colour	Homelight
CRI (Ra)	80
Dimmable	No
EAN code	5410288271828
Energy class	A++
Equivalent watt (W)	25
Cap/Base	B22
Type	ToLEDo Retro Candle
Watt (Nominal) (W)	2
Light colour	Homelight
Ordering number	0027182
Efficacy (Rated) (lm/w)	125
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	250
Technology	LED
Voltage (V)	230-240
Colour consistency (SDCM)	6

## DATA TABLE

## ToLEDo Retro Candle

ToLEDo RT Candle 250LM B22 SL

**0027182**

### General data

<b>Average life (Nominal) (h)</b>	15000
<b>Control gear required</b>	No
<b>Lamp finish</b>	Clear
<b>Lamp shape</b>	Candle
<b>Control gear availability</b>	No
<b>Dimmable</b>	No
<b>Dry applications use only</b>	Yes
<b>EAN code</b>	5410288271828
<b>Energy class</b>	A++
<b>Energy saving lamp</b>	Yes
<b>General application</b>	Hospitality; Residential & Consumer
<b>Intended purpose</b>	No
<b>Cap/Base</b>	B22
<b>Lamp mercury content (mg)</b>	0
<b>Type</b>	ToLEDo Retro Candle
<b>No. of switching cycles before premature failure (min)</b>	>50,000
<b>Optimal operating condition (°C)</b>	25
<b>Ordering number</b>	0027182
<b>Range features</b>	<p>LED Chip technology using a virtual filament design which creates a warm ambiance similar to traditional lamps            First lamp of its type to achieve A++ rating - up to 134 lm/W            Suitable for replacement of up to 60W incandescent lamps            Available in clear and satin versions            Packed in individual boxes (SL) or in blisters (BL)            Up to 90% energy saving compared to incandescent lamps            Cooler burning versus standard LED lamps            Dimensional compatibility with all fixtures            Average lifetime from 6000 hours up to 15 000 hours            3 years warranty  <b>WARNING :</b> If the outer glass jacket is broken conductive parts may still be active. Lamps must not be touched before making sure the mains cable is not live. Switch off the main electrical supply before replacing lamp!</p>
<b>Product name</b>	ToLEDo RT Candle 250LM B22 SL
<b>Average life (Rated) (h)</b>	15000
<b>Special purpose lamp</b>	No
<b>Starting time (max) (s)</b>	0.05
<b>Technology</b>	LED
<b>Transformer required</b>	No
<b>Warm-up time to 60% of full light (max) (s)</b>	< 1s => 60%

### Optical data

<b>Chromaticity coordinate X</b>	-1
----------------------------------	----

## ToLEDo Retro Candle

ToLEDo RT Candle 250LM B22 SL

0027182

Chromaticity coordinate Y	-1
Colour temperature (K)	2700
CRI (Ra)	80
Light colour	Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	250
Luminous flux (Rated) (lm)	250
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6


### Physical data

Colour	Homelight
Diameter (mm)	38
Max. Lamp Diameter (mm) - D	35
Lamp Length (mm) - C/L	91
Lamp dimension equal to filament lamp equivalent	Yes

### Electrical data

Current (A)	20
Drive current (mA)	20
Equivalent watt (W)	25
kWh per 1000 hours burning time	2
Lamp power factor	0.5
Watt (Nominal) (W)	2
Efficacy (Rated) (lm/w)	125
Watt (Rated) (W)	2
Voltage (V)	230-240

## TECHNICAL DRAWINGS



## ToLEDo Retro Candle

ToLEDo RT Candle 250LM B22 SL

**0027182**

