

ToLEDo Retro Candle Dimmable

TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL

0027496



Product features

- Perfect for decorative and general lighting applications and creates a warm ambiance similar to traditional lamps
- Same look, size and functionality as incandescent lamps
- The combination of innovative filament chip technology and dimming functionality make it an ideal solution for both hospitality application and for general lighting
- Suitable for replacement of 40W incandescent lamp
- A++ energy rating - 104 lm/W
- Dimming functionality helps to vary lighting scene as lamps can be dimmed from 100% to 10% and reduces energy consumption as well
- Sparkling light output
- Omni-directional light distribution
- Environment friendly - no mercury and lower CO2 emissions
- Dimmable on approved dimmers
- Color temperature - 2700K Homelight



PRODUCT OVERVIEW

Product code	0027496
Product name	TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL
Technology	LED
Watt (Rated) (W)	4.5
Lamp shape	Candle
Type	ToLEDo Retro Candle Dimmable
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Certifications	EUTIE103
ETIM Class	EC001959
E-number Finland	4740509
E-number Sweden	8292846
Luminous flux (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Wattage (W)	4.5
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288274966

DATA TABLE

General data

Product code	0027496
Product name	TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL
Technology	LED
Watt (Rated) (W)	4.5

ToLEDo Retro Candle Dimmable

TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL

0027496

Lamp shape	Candle
Type	ToLEDo Retro Candle Dimmable
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Operating Temperature Range (°C)	45
Certifications	EUTIE103
ETIM Class	EC001959
E-number Finland	4740509
E-number Sweden	8292846

Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Adjustable chromaticity	N
Beam angle (Rated) (°)	320

Electrical data

Wattage (W)	4.5
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.8
No. Of switching cycles before premature failures	50000
Transformer required	Yes
Lamp Energy Label (class)	A++
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	92
Nominal Product Diameter (mm)	35
Weight (kg)	0.16

Packaging

Single packaging type	Carton
------------------------------	--------

ToLEDo Retro Candle Dimmable

TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL



0027496

Product EAN number	5410288274966
Packaging single length (cm)	4.2
Packaging single width (cm)	4.2
Packaging single height (cm)	10.5
DUN14 (inner)	25410288274960
Units per inner package	6
Packaging inner length (cm)	12.5
Packaging inner width (cm)	9.4
Packaging inner height (cm)	13.8
DUN14 (outer)	15410288274963
Units per outer package	60
Packaging outer length (cm)	49.5
Packaging outer width (cm)	29.5
Packaging outer height (cm)	15.5

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures



PHOTOMETRY




ToLEDo Retro Candle Dimmable

TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL

0027496



TECHNICAL DRAWINGS



ToLEDo Retro Candle Dimmable

TOLEDO RT DIM V2 CAV2 CL 470LM 2700K E27 SL

0027496

