

ToLEDo Retro Ball Dimmable

ToLEDo RT Dim Ball 470LM E14 SL

0027250



PRODUCT OVERVIEW

Product code	0027250
Product name	ToLEDo RT Dim Ball 470LM E14 SL
Technology	LED
Watt (Rated) (W)	4.5
Lamp shape	Ball
Type	ToLEDo Retro Ball Dimmable
Cap/Base	E14
Lamp finish	Clear
General application	Hospitality, Residential & Consumer
Certifications	EUTIE103
ETIM Class	EC001959
E-number Finland	4740433
E-number Sweden	8295005
Luminous flux (lm)	470
Efficacy (lm/w)	104.44
Colour temperature (K)	2700
Light colour	Homelight
Colour Consistency (SDCM)	6
Wattage (W)	4.5
Average life (Nominal) (h)	15000
Product EAN number	5410288272504

DATA TABLE

General data

Product code	0027250
Product name	ToLEDo RT Dim Ball 470LM E14 SL
Technology	LED

ToLEDo Retro Ball Dimmable

ToLEDo RT Dim Ball 470LM E14 SL

0027250

Watt (Rated) (W)	4.5
Lamp shape	Ball
Type	ToLEDo Retro Ball Dimmable
Cap/Base	E14
Lamp finish	Clear
General application	Hospitality, Residential & Consumer
Certifications	EUTIE103
ETIM Class	EC001959
E-number Finland	4740433
E-number Sweden	8295005

Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Efficacy (lm/w)	104.44
Colour temperature (K)	2700
Correlated colour temperature range (K)	2700
Light colour	Homelight
Colour Consistency (SDCM)	6
Adjustable chromaticity	N
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	4.5
Equivalent watt (W)	40
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Mains voltage (V)	220-240V~
Lamp power factor	0.8
Control gear required	No
No. Of switching cycles before premature failures	>50000
Transformer required	No
Drive current (mA)	27
Lamp Energy Label (class)	A++
Energy efficiency level	A++
kWh per 1000 hours burning time	5

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

ToLEDo Retro Ball Dimmable

ToLEDo RT Dim Ball 470LM E14 SL

0027250

Physical data

Max. Lamp Diameter (mm) - D	45
Weight (kg)	0.033


Packaging

Single packaging type	Carton
Product EAN number	5410288272504
Packaging single length (cm)	4.8
Packaging single width (cm)	4.8
Packaging single height (cm)	11.7
DUN14 (inner)	25410288272508
Units per inner package	6
Packaging inner length (cm)	13.7
Packaging inner width (cm)	10.6
Packaging inner height (cm)	15.7
DUN14 (outer)	15410288272501
Units per outer package	60
Packaging outer length (cm)	55.5
Packaging outer width (cm)	33.3
Packaging outer height (cm)	16.7

Safety data

Breakage cleaning instructions	Not applicable
Recommendation for disposal at end of life	Not applicable
Special purpose lamp	No
Intended purpose	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Suitable for accent lighting	Yes

TECHNICAL DRAWINGS



ToLEDo Retro Ball Dimmable

ToLEDo RT Dim Ball 470LM E14 SL

0027250

