

RefLED ES50 V3

RefLED ES50 V3 3.5W 250lm 830 36° SL

0027427



Range Features

- Up to 90% energy saving comparing to halogen.
- High light output - real retrofit for the halogen lamps (36W, 50W and 60W replacements).
- Perfect shape and size for a perfect fit in your luminaire.
- Choice of beam angles to suit lighting needs (36 degree or ultra wide beam 110 degree).
- Available in different colour temperatures: 2700K Homelight, 3000K Warm white, 4000K Cool white and 6500K Daylight.
- Dimmable option available on approved dimmers *.
- Highly efficient - up to 71Lm/W.
- Average rated life of 15,000 hours.
- 3 year Warranty.

PRODUCT OVERVIEW

Lamp finish	White
Lamp shape	GU10/ES50
Colour temperature (K)	3000
CRI (Ra)	80
Dimmable	No
EAN code	5410288274270
Energy class	A+
Equivalent watt (W)	36
Beam angle(°)	36
Type	RefLED ES50 V3
Watt (Nominal) (W)	3.6
Light colour	830 Warm White
Ordering number	0027427
Efficacy (Rated) (lm/w)	66.66
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	240
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (Nominal) (h)	15000
Control gear required	No
Lamp finish	White
Lamp shape	GU10/ES50

RefLED ES50 V3

RefLED ES50 V3 3.5W 250lm 830 36° SL

0027427

Control gear availability	No
Dimmable	No
EAN code	5410288274270
Energy class	A+
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	General lighting
Lamp mercury content (mg)	0
Type	RefLED ES50 V3
No. of switching cycles before premature failure (min)	12500
Optimal operating condition (°C)	25
Ordering number	0027427
Range features	<p>Up to 90% energy saving comparing to halogen. High light output - real retrofit for the halogen lamps (36W, 50W and 60W replacements). Perfect shape and size for a perfect fit in your luminaire. Choice of beam angles to suit lighting needs (36 degree or ultra wide beam 110 degree). Available in different colour temperatures: 2700K Homelight, 3000K Warm white, 4000K Cool white and 6500K Daylight. Dimmable option available on approved dimmers *. Highly efficient - up to 71Lm/W. Average rated life of 15,000 hours. 3 year Warranty.</p>
Product name	RefLED ES50 V3 3.5W 250lm 830 36° SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	<0,5
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 2s => 95%
Product features	<p>Good every day quality from a brand you can trust. RefLED ES50 V3 delivers a cost effective solution to replacing halogen GU10 with LED offering 240lm of light equivalent to a 36W halogen lamp while extending lamp life to 15,000 hours. GU10 cap. 36 degree beam angle in warm white 3000K. Backed by a 3 year warranty. CCSMD Technology delivers a halogen look lens with high efficiency and good thermal control.</p>

Optical data

Chromaticity coordinate X	0.437
Chromaticity coordinate Y	0.404
Colour temperature (K)	3000
CRI (Ra)	80
Beam angle(°)	36

RefLED ES50 V3

RefLED ES50 V3 3.5W 250lm 830 36° SL

0027427

Light colour	830 Warm White
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	240
Peak intensity (cd)	570
Luminous flux (Rated) (lm)	240
Suitable for accent lighting	Yes
Beam angle (Rated) (°)	36
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Current (A)	36
Equivalent watt (W)	36
kWh per 1000 hours burning time	4
Lamp power factor	0.4
Watt (Nominal) (W)	3.6
Efficacy (Rated) (lm/w)	66.66
Watt (Rated) (W)	74
Voltage (V)	220-240

Physical data

Max. Lamp Diameter (mm) - D	50
Lamp Length (mm) - C/L	54
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Fluorescent lamp replacement	No

RefLED ES50 V3

RefLED ES50 V3 3.5W 250lm 830 36° SL

0027427

