

ToLEDo G4

ToLEDo G9 200LM 827 SL

0026506

Range Features



PRODUCT OVERVIEW

Lamp finish	Frosted
Lamp shape	Capsule
Colour temperature (K)	2700
CRI (Ra)	80
Dimmable	No
EAN code	5410288265063
Energy class	A+
Cap/Base	G9
Type	ToLEDo G9
Watt (Nominal) (W)	3
Light colour	827 Homelight
Ordering number	0026506
Efficacy (Rated) (lm/w)	66.66
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	80
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (Nominal) (h)	15000
Control gear required	No
Lamp finish	Frosted
Lamp shape	Capsule
Dimmable	No
Dry applications use only	Yes

ToLEDo G4

ToLEDo G9 200LM 827 SL

0026506

EAN code	5410288265063
Energy class	A+
Energy saving lamp	Yes
Fixture rating	Open
General application	Hospitality; Residential & Consumer
Intended purpose	General lighting
Cap/Base	G9
Lamp mercury content (mg)	0
Type	ToLEDo G9
No. of switching cycles before premature failure (min)	15000
Optimal operating condition (°C)	25
Ordering number	0026506
Product name	ToLEDo G9 200LM 827 SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%

Optical data

Chromaticity coordinate X	-1
Chromaticity coordinate Y	-1
Colour temperature (K)	2700
CRI (Ra)	80
Light colour	827 Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	200
Luminous flux (Rated) (lm)	80
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Drive current (mA)	29
kWh per 1000 hours burning time	3
Lamp power factor	0.4
Watt (Nominal) (W)	3
Efficacy (Rated) (lm/w)	66.66
Watt (Rated) (W)	3
Voltage (V)	220-240

ToLEDo G4

ToLEDo G9 200LM 827 SL

0026506

Physical data

Max. Lamp Diameter (mm) - D	17
Lamp Length (mm) - C/L	51

