

ToLEDo G4

ToLEDo G4 2W 140LM 827 SL

0026504



Range Features

-



PRODUCT OVERVIEW

Lamp finish	Frosted
Lamp shape	Capsule
Colour temperature (K)	2700
Colour	Homelight
CRI (Ra)	80
Dimmable	No
EAN code	5410288265049
Energy class	A+
Cap/Base	G4
Type	ToLEDo G4
Watt (Nominal) (W)	2
Light colour	Homelight
Ordering number	0026504
Efficacy (Rated) (lm/w)	70
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	140
Technology	LED
Voltage (V)	12V AC
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (Nominal) (h)	15000
Control gear required	No
Lamp finish	Frosted
Lamp shape	Capsule
Control gear availability	No
Dimmable	No

ToLEDo G4

ToLEDo G4 2W 140LM 827 SL

0026504

Dry applications use only	Yes
EAN code	5410288265049
Energy class	A+
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	G4
Lamp mercury content (mg)	0
Type	ToLEDo G4
No. of switching cycles before premature failure (min)	15000
Optimal operating condition (°C)	25
Ordering number	0026504
Product name	ToLEDo G4 2W 140LM 827 SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%

Optical data

Colour temperature (K)	2700
CRI (Ra)	80
Light colour	Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	140
Luminous flux (Rated) (lm)	140
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Physical data

Colour	Homelight
Diameter (mm)	14
Max. Lamp Diameter (mm) - D	14
Lamp Length (mm) - C/L	36
Lamp dimension equal to filament lamp equivalent	Yes

Electrical data

Current (A)	90
--------------------	----

ToLEDo G4

ToLEDo G4 2W 140LM 827 SL

0026504

Drive current (mA)	240
kWh per 1000 hours burning time	3
Lamp power factor	0.7
Watt (Nominal) (W)	2
Efficacy (Rated) (lm/w)	70
Watt (Rated) (W)	2
Voltage (V)	12V AC

