



### UB-Series Cable Ties

#### Commercial Grade Cable Ties

Cable ties fit for all purposes manufactured in PA66 material.

#### Features and Benefits

- A range of commercial grade cable ties
- Available in black or natural



A range of cable tie bases are also available please see page 10




For more products in this range see Section 1.1 in our Product Catalogue.



For more information on tooling please refer to the Application Tooling chapter in the Product Catalogue



Commercial Grade Cable Ties.

TYPE	Width (W) mm	Length(L) mm	Bundle Ø max.mm	 N	Material	Colour	Pack Cont.	Packs per Carton	Article-No.
UB100A-B	2.5	100	22	80	PA66	Black (BK)	100	320	138-00000
UB100A-N	2.5	100	22	80	PA66	Natural (NA)	100	320	138-00001
UB140A-B	2.5	140	35	80	PA66	Black (BK)	100	250	138-00019
UB140A-N	2.5	140	35	80	PA66	Natural (NA)	100	250	138-00020
UB200A-B	2.5	200	55	80	PA66	Black (BK)	100	130	138-00021
UB200A-N	2.5	200	55	80	PA66	Natural (NA)	100	130	138-00022
UB150B-B	3.5	150	35	135	PA66	Black (BK)	100	100	138-00044
UB150B-N	3.5	150	35	135	PA66	Natural (NA)	100	100	138-00045
UB200B-B	3.5	198	50	135	PA66	Black (BK)	100	80	138-00025
UB200B-N	3.5	198	50	135	PA66	Natural (NA)	100	80	138-00026
UB160C-B	4.6	160	35	225	PA66	Black (BK)	100	80	138-00027
UB160C-N	4.6	160	35	225	PA66	Natural (NA)	100	80	138-00028
UB200C-B	4.6	200	50	225	PA66	Black (BK)	100	60	138-00046
UB200C-N	4.6	200	50	225	PA66	Natural (NA)	100	60	138-00047
UB250C-B	4.6	245	65	225	PA66	Black (BK)	100	60	138-00006
UB250C-N	4.6	245	65	225	PA66	Natural (NA)	100	60	138-00007
UB270C-B	4.6	270	73	225	PA66	Black (BK)	100	60	138-00034
UB270C-N	4.6	270	73	225	PA66	Natural (NA)	100	60	138-00033
UB300C-B	4.6	300	85	225	PA66	Black (BK)	100	50	138-00008
UB300C-N	4.6	300	85	225	PA66	Natural (NA)	100	50	138-00009
UB385C-B	4.6	390	110	225	PA66	Black (BK)	100	40	138-00050
UB385C-N	4.6	390	110	225	PA66	Natural (NA)	100	40	138-00051
UB385E-B	7.6	390	100	535	PA66	Black (BK)	100	20	138-00012
UB385E-N	7.6	390	100	535	PA66	Natural (NA)	100	20	138-00013
UB760E-B	7.6	760	225	535	PA66	Black (BK)	100	20	138-00041
UB760E-N	7.6	760	225	535	PA66	Natural (NA)	100	20	138-00042
UB540H-B	13.0	535	150	535	PA66	Black (BK)	50	12	138-00014
UB540H-N	13.0	535	150	535	PA66	Natural (NA)	50	12	138-00043