

PDU-8WS-V-UK-M-SP-1U

Modular  
Surge Protected Input  
Vertical 8-Way UK Socket  
Plus IEC C-20  
Input Socket



**Modular Power Input Flex Options**

**8-Way UK Power Sockets**



Telecom & Networking



Data centres & Server farms



Broadcast & A/V



HVAC & Industrial

**Modular Power Distribution - Select **Your** Power Input Cable**

**Looking for a more 'tailor made' power solution for your data cabinet or other power requirements?**

The new LMS Data range of fully modular power input PDUs is your ideal solution. Allowing for you, the customer to choose the length of input power cordage for the LMS Data PDU plus you can also choose the power socket such as UK Plug, heavy-duty commando 16/32Amp, IEC-14 for example.

Having the correct cordage length and power socket means you can now not only cut down installation deployment but also get a much tidier installation within the data cabinet, freeing up valuable space and reducing clutter, thus increasing system uptime.

Like the complete LMS Data PDU lineup, both quality and a long service life is built in, together with enhanced ergonomics including a robust, illuminated rocker switch, 1U high profile and supplied cage nuts and bolts.

**specifications:**

Modular Power Input Power Distribution - IEC C-20 Socket

High-Density 8-Way Standard UK Power Outlet Sockets

Integral Surge Protection and Earth (Ground) Validation LEDs

Vertical, low profile design

Choose your Power Input Cable Length and Socket Type\*\*

Robust, black aluminium design for industrial use

Neon on/off power switch for assured control

Maximum power rating - 4000W, 13 Amps nominal\*



\* Electrical Specifications Nominal  
\*\*Ask for Power Input Cable Options



Copyright 2015 LMS Data  
All trademarks acknowledged E&OE.  
Details subject to change

