

**NEW FOR 2017!**

**PROSAFE**

**STRENGTH AND ENDURANCE**



BE-02+

High Quality Warm Knitted Beanie Hat with Integrated USB Rechargeable LED Light

ALSO IDEAL AS A HANDY KEY-FOB



Orange: BE-02+0 / Black: BE-02+ / Yellow: BE-02+Y



INTEGRATED MALE USB



EASY TO REMOVE FROM BEANIE



CHARGE DIRECTLY FROM USB PORT - RED TO GREEN



SUPPLIED READY MERCHANDISED



HIGH POWERED 150 LUMEN OUTPUT



4 X HIGH POWERED SMD LEDS - 150 LUMEN

2½-6% HOURS RUNTIME | 13 METRE BEAM RANGE | 150 LUMENS OUTPUT | IPX5 WATER RESISTANCE



- » 4 x high powered cool white 6500k Samsung SMD LEDs - 150 Lumen
- » 420mAh Lithium-polymer battery
- » Press once to turn on and toggle between 3 light intensity levels. HIGH > LOW > 2 Hz FLASH > OFF

- » Can be fully charged in 4 hours
- » Material: 35% acrylic 65% polyester, machine washable at 30°
- » Ideal for: Runners, Walkers, Camping, Plumbers, Electricians, Tradesman and Contract Engineers



PS-HDL1

160 Lumen CREE LED Headlight with 200 Lumen Boost with 2 x AAA Energizer



LIGHT BY CREE LEDs

5-30 HOURS RUNTIME | 90 METRE BEAM RANGE | 200 LUMENS OUTPUT | IPX6 WATER RESISTANCE

- » 160 Lumen white CREE LED with a 200 Lumen output on BOOST
- » 3 main functions - Boost / High / Low
- » 1 auxiliary function - High
- » Easy push button micro switch

- » Ultra-smooth reflector
- » 45° rotational head
- » Fully adjustable non-slip silicone headband
- » IPX6 water resistant

PS-HDL2



200 Lumen CREE LED Helmet Mountable Headlight with 3 x AAA Energizer

5-120 HOURS RUNTIME | 90 METRE BEAM RANGE | 200 LUMENS OUTPUT | IPX6 WATER RESISTANCE

LIGHT BY CREE LEDs

- » 200 Lumen white CREE LED
- » 4 main functions - High / Medium / Low / SOS flashing
- » 3 auxiliary function - High / Low / Strobe Flashing
- » Easy push button micro switch

- » Ultra-smooth reflector
- » 45° rotational head
- » Fully adjustable headband
- » Attach to industrial or sports helmet with 3M pad (included)
- » IPX6 water resistant

PS-CL1

USB Rechargeable Clip & Keyring Light with 50 Lumen White LED & 2 Red LEDs

ALSO IDEAL AS A HANDY KEY-FOB



LANYARD INCLUDED



HANDY KEY-FOB LIGHT



MICRO-USB RECHARGEABLE

1.3-3.2 HOURS RUNTIME | 15 METRE BEAM RANGE | 50 LUMENS OUTPUT | IPX4 WATER RESISTANCE



- » 50 Lumen white Nichia LEDs
- » 3 White functions - High/Low/Strobe
- » 3 Red functions - High/Strobe/Signal
- » Easy push button micro switch
- » Micro-USB rechargeable (cable included)

- » Elasticated lanyard (included)
- » Strong rear clip for easy attachment to many items
- » Elasticated loop & non-slip pad - perfect for attaching to bicycle handles
- » Small and ultra lightweight