

STRENGTH AND ENDURANCE...



SLR-3000

3-6
HOURS RUNTIME

25
METRE BEAM RANGE

3000
LUMEN OUTPUT

IPX4
WATER RESISTANCE



- 3000 Lumen Samsung SMD LEDs
- Powerful Li-ion battery with battery level indicator
- Battery pack can easily be removed and used as a USB power bank
- 50% dimming function to increase battery runtime
- Built in aluminium heat sink
- Anti-slip rubber grip handle
- Adjustable head for light angle
- Tough polycarbonate housing and stand
- Acrylic LED diffuser for even light dispersion
- Anti glare polycarbonate lens
- SL-251 adjustable tripod available



PS-PL4R

2
HOURS RUNTIME

3
METRE BEAM RANGE

125
LUMEN OUTPUT

IPX4
WATER RESISTANCE



MICRO-USB CHARGING CABLE

2 X CREE SMD LEDs

LIGHT BY
CREE
LEDs

USB
CHARGING

- 125 Lumen White Cree SMD LEDs
- Tough ABS housing is high-vis yellow for easy visibility
- Pocket clip for easy transportation
- Strong magnet within the body for easy attachment and hands-free use
- Non-slip grips
- Easy press tactical micro switch
- Micro-USB charging cable included for portable non-static charging
- Red-to-Green charging indicator
- Charging port with protective cover
- IPX4 water resistant
- Impact resistant to 1m

PS-CAP1

2 1/2-25
HOURS RUNTIME

34
METRE BEAM RANGE

125
LUMEN OUTPUT

IPX5
WATER RESISTANCE



CAN BE CLIPPED ONTO MANY ITEMS OTHER THAN A CAP



USB
CHARGING

- Powerful 125 Lumen white LED
- 2 x 5mm Red LEDs - on and flashing
- Micro-USB rechargeable
- Multi-faceted reflector
- Can be fully charged in 4 hours
- Strong ABS housing
- 120° rotational head
- Easy push micro switch
- IPX5 water resistant
- Red-to-Green charging indicator
- Ideal for all

The universal PS-CAP1 easily slots on the peak of a baseball cap or other items such as garments and cables, it produces 125 Lumen white output but also has 2 red LEDs

PS-IL5R



3-7
HOURS RUNTIME

52
METRE BEAM RANGE

500
LUMEN OUTPUT

IP54
DUST+ WATER RESISTANCE



COMPACT HAND-HELD SIZE



USEFUL MAGNET & HOOK



USB
CHARGING

- 500 Lumen White Samsung SMD LEDs
- Additional 200 Lumen torch in the head
- Ultra strength aluminium and polycarbonate housing
- Integral pocket clip and strong magnets for hands-free use
- Protective charge point cover
- DC-USB charging cable (included) for portable non-static charging
- Red-to-Green charging indicator
- IP54 dust and water resistant
- Impact resistant to 1m

PS-IL10R



3-32
HOURS RUNTIME

64
METRE BEAM RANGE

1000
LUMEN OUTPUT

IP54
DUST+ WATER RESISTANCE



SMOOTH EVEN LIGHT SPREAD



DC-USB CABLE INCLUDED



USB
CHARGING

- 1000 Lumen White Samsung SMD LEDs
- Additional 250 Lumen torch in the head
- Ultra strength aluminium and polycarbonate housing
- Integral hanging hook and strong magnet for hands-free use
- Multi positional hook / foldable kick stand
- DC-USB charging cable (included) for portable non-static charging
- Red-to-Green charging indicator
- IP54 dust and water resistant
- Impact resistant to 1m

IL-SIG1



4 1/2-24
HOURS RUNTIME

52
METRE BEAM RANGE

600
LUMEN OUTPUT

IP54
DUST+ WATER RESISTANCE



RED / AMBER / GREEN LEDs



100 LUMEN TORCH IN HEAD



USB
CHARGING

- 600 Lumen white Samsung SMD LEDs
- Red / Amber / Green LEDs for signalling
- 4 independent operation switches
- DC-USB charging cable (included)
- 100 Lumen torch in the head
- Ultra strength aluminium and polycarbonate housing
- Red-to-Green charging indicator
- Integral hanging hook & magnet for hands-free use
- Multi positional hook / foldable kick stand
- Impact resistant to 1m

BE SAFE... BE SEEN...



SV-01 Y/O



EN ISO 20471:2013



EN ISO 14116:2015



ALSO IDEAL AS A
HANDY KEY-FOB

Available in **Hi-Vis Yellow (SV-01Y)**
or **Hi-Vis Orange (SV-01O)**
& also various sizes - L, XL, XXL




INTEGRATED MALE USB



SMALL & COMPACT



CHARGE DIRECTLY FROM USB
PORT - RED-TO-GREEN LIGHTS



- Class 2 high visibility vest (conforms to EN ISO 20471:2013) with USB rechargeable light
- 4 x high powered cool white 6500K Samsung SMD LEDs - 150 Lumen
- 420mAh Lithium-polymer battery
- Gives between 2.5 and 6.5 hours

- Easily removed from the vest and charged directly through a USB port
- Fire Retardant to EN ISO 14116:2015
- Can be fully charged in 4 hours
- Press once to turn on and toggle between 3 light intensity levels. HIGH > LOW > 2 Hz FLASH > OFF

SPORT-H1



LIGHT BY **CREE** LEDs
EMERGENCY FLASH

- 175 Lumen white CREE LED
- 2 x 5mm Red LEDs
- 2Hz safety and SOS flashing modes
- 5 main mode functions - HIGH > MED > LOW > SOS FLASHING > HIGH RED > RED 2Hz FLASHING > OFF
- Multi-faceted deep reflector
- Easy push micro switch
- 45° rotational head
- Strong ABS housing
- Fully adjustable silicone lined headband
- 1m impact resistant
- Ideal for Runners
- Neon Pink / Yellow / Blue / Green

PS-HDL6R



- 350 Lumen white Samsung SMD LEDs
- Dual power options - runs off rechargeable lithium battery or 3 x AAA alkaline batteries
- 3M VHB adhesive helmet mount (inc)
- Easy push button micro switch
- Anti-dazzle retractable light shield
- 1800mAh Li-polymer direct micro-USB rechargeable battery pack (included)
- 3 x AAA Battery case (included)
- Fully adjustable non-slip silicone headband
- IPX6 water resistant
- Impact resistant to 1m

PS-HDL9R



- 750 Lumen white CREE LED
- High power Li-ion batteries (included)
- Parallel circuitry - runs off 1 or 2 batteries
- Micro-USB rechargeable (cable included)
- Anti-dazzle retractable light shield
- Wider angle light spread
- Easy twist smooth dimming power switch
- Red rear battery pack light (on & flash)
- 45° rotational head
- Fully adjustable non-slip silicone headbands
- Presented in hard zipped storage case



T +00[44] 1527 584 344
E sales@unilite.co.uk

F +00[44] 1527 584 345
W www.unilite.co.uk