



Overview

Model Name	APC Personal SurgeArrest, 8 outlet, phone line protection
Includes	1.8 Meter Tel cable (2) , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Mexico , United States

Output

Number of Outlets	8
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Power	0 W
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	6 feet (1.83 meters)
Maximum Input Current	0 A

Surge Protection and Filtering

Surge energy rating	240 Joules
EP Joule Rating	1060 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	60.0 dB
Peak Current Normal Mode	6.5 kA
Peak Current Common Mode	13.0 kA
NM Surge Response Time (ns)	0.0 NS
Data Line Protection	RJ-11 Modem/Fax protection (two wire single line)
Data Lines Protected(multi-line only)	1
Let Through Voltage Rating	300

Physical

Net Weight	1.8 lbs (0.82 kg)
Maximum Height	1.76 inches (44.0 mm)
Maximum Width	8.0 inches (203.0 mm)
Maximum Depth	5.76 inches (146.0 mm)
Shipping Weight	2.3 lbs (1.06 kg)
Shipping Height	2.0 inches (51.0 mm)
Shipping Width	12.5 inches (318.0 mm)
Shipping Depth	6.26 inches (159.0 mm)
Master Carton Units	12.0
Master Carton Weight	29.0 lbs
SCC Codes	10731304014413
Color	Beige
Units per Pallet	240.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA , UL 1283 , UL 1363 , UL 1449 , UL 497A
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000
UL 1449 TVSS Rating	330