



Main

Range of product	Linery
Product or component type	Cable end
Cable end size	Long
Standards	NF C 63-023
Type of packing	Bag
Quantity per set	Set of 100
Cable cross section	0.02 in ² (10 mm ²)

Complementary

Cable end type	Single conductor
Additional information	For additional marker tag holder
Color	Brown
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 8
Bezel size	Ø 8.4 mm
Tube diameter	4.9 mm
Length	1.1 in (28 mm)
Tube length	18 mm
CAD overall width	0.31 in (8 mm)
CAD overall height	0.39 in (10 mm)
CAD overall depth	1.1 in (28 mm)
Product weight	0.19 lb(US) (0.085 kg)

Environment

Ambient air temperature for operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901535577
Nbr. of units in pkg.	100
Package weight(Lbs)	0.17999999999999999
Returnability	N
Country of origin	DE

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0437 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------