

Product data sheet

Characteristics

1S43F

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Buck and Boost Transformer
Box number	7A
NEMA degree of protection	NEMA 3R
Insulation temperature	356 °F (180 °C)
Primary voltage	120 x 240 V
Rated power in VA	1 kVA
Secondary voltage	12/24 V
Temperature rise	115 °C

Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901876311
Nbr. of units in pkg.	1
Package weight(Lbs)	25.66
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
